



BIRNS Model 4121 Doubly-Safe Chamber Light™

Options You can customize your new BIRNS Chamber Light, often at no extra cost, to make it ideal for your own requirements. These options are:

- Lamp: Please see lamp table below
- Lens: Please see lens table below.

Lamp Options Notes:

1. Unless specified otherwise, the default "standard" installed in the Chamber Light is 32C-001.
2. These are the most popular lamps, but others are available. (Applicable Standards' heat output limitations restrict us to max. 50w lamps.) Contact us for details.
3. All Chamber Light lamps operate well on AC or DC.

Lamp Part No.	Volts	Watts	Amps	Color (K)	Output (Lumens)	Rated Life (Hours)
32C-001	12	20	1.7	2,925	260	3,000
32C-002	12	50	4.2	3,050	895	3,000
32C-024	24	20	0.9	TBD	TBD	TBD
32C-025	24	35	1.5	TBD	TBD	TBD
32C-015	30	50	1.7	TBD	TBD	TBD



Lens Options

Changing the lens is very quick and simple.

Lens	Part No.	Benefit	Application
Clear	35A-007	Greatest light output	General illumination
Frosted	35A-009	Diffuses light beam	Makes "softer" white light
Blue	35A-011	Approximates daylight color	Good for 'ambient' lighting
Blue-Frosted	35A-012	Diffused 'Daylight' color	Makes "softer" blue light