



BIRNS Model 4132 General-Area Chamber Light™

Equipment: The BIRNS General-Area Chamber Light comes complete with a 1.8m (6') power cable installed. However, for a different cable length, please specify and BIRNS can tailor it to any length or configuration.

Options Variations on the BIRNS General-Area Chamber Light are available as follows:

- Model **4132**: with a 1.8m (6') power cable installed
- Model **4133**: like 4132 but with an On/Off switch
- Model **4134**: like 4132 but with a male connector and 63A-013 SS locking sleeve on the cable
- Model **4135**: like 4132 but with a switch, male connector and 63A-013 SS locking sleeve on the cable

Customize the BIRNS General Area Chamber Light, often at no extra cost, to tailor it to specifications. These options are:

- Lamp: Please see lamp table below
- Lens: Please see lens table below.

Lamp Options Notes:

1. Unless specified otherwise, the default "standard" installed in Model 4132 Chamber Light is 32K-003.
2. These are the most popular lamps, but others may be available. Contact us for details.
3. All Chamber Light lamps operate well on AC or DC.



Lamp Part No.	Volts	Watts	Color (K)	Output (Lumens)	Rated Life (Hours)
32K-002	12	23	TBD	TBD	3,000
32K-003	28	28	TBD	TBD	3,000
32K-004	12	7.5	TBD	TBD	TBD
32K-005	12	14	TBD	TBD	TBD
32K-006	24	14	TBD	TBD	TBD

Dome Options: Changing the dome is very quick and simple.

Lens	Part No.	Benefit	Application
Clear	35B-034	Greatest light output	General illumination
Frosted	TBD	Diffuses light	General illumination
Amber	TBD	Softens, colors light beam	TBD
Red	TBD	Prevents night blindness	TBD